



T5 High Output

F39T5/841/HO/ALTO 40PK

Philips T5 HO lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information	
Cap-Base	G5
Features	HO Alto® [High Output Alto]
Light Technical	
Color Code	841 [CCT of 4100K]
Luminous Flux	3,500 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4100 K
Luminous Efficacy (rated) (Nom)	82 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	38.0 W
Lamp Current (Nom)	0.325 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5
Net Weight (Piece)	0.172 lb
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	39W/841 Min Bipin T5 HO ALTO UNP
Full product name	F39T5/841/HO/ALTO 40PK
Order code	290254
Material Nr. (12NC)	927992684022
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677290252
Numerator - Packs per outer box	40
EAN/UPC - Case	50046677290257


T5 High Output

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
39W/841 Min Bipin T5 HO	11/16 inch	33-7/16 inch	33-3/4 inch	33-5/8 inch	34 inch
ALTO UNP					

Photometric data




Spectral Power Distribution Colour - 39W/841 Min Bipin T5 HO ALTO UNP

Lifetime



Life expectancy diagram - 3 hour cycle



Lumen Maintenance Diagram - 39W/841 Min Bipin T5 HO ALTO UNP

T5 High Output

Lifetime

Life expectancy diagram - 12 hour cycle

