

T5 High Output

F54T5/865/HO/ALTO 40PK

Philips T5 HO lamps are environmentally-responsible, ultra-slim and have extraordinary light output and longer life.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information	
Cap-Base	G5
Features	HO Alto® [High Output Alto]
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	4,650 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6300 K
Luminous Efficacy (rated) (Nom)	77 lm/W
Color rendering index (CRI)	82
Operating and Electrical	
Power Consumption	54.1 W
Lamp Current (Nom)	0.455 A
Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Shape	T5
Net Weight (Piece)	0.23 lb
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Product Data	
Order product name	F54T5/865/HO/ALTO 40PK
Full product name	F54T5/865/HO/ALTO 40PK
Order code	147454
Material Nr. (12NC)	927993186522
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677147457
Numerator - Packs per outer box	40
EAN/UPC - Case	50046677147452


T5 High Output

Dimensional drawing




Product	D (max)	A (max)	B (max)	B (min)	C (max)
F54T5/865/HO/ ALTO 40PK	11/16 inch	45-1/4 inch	45-9/16 inch	45-7/16 inch	45-13/16 inch

Photometric data




Spectral Power Distribution Colour - F54T5/865/HO/ALTO 40PK

Lifetime



Life expectancy diagram - 3 hour cycle



Lumen Maintenance Diagram - F54T5/865/HO/ALTO 40PK

T5 High Output

Lifetime

Life expectancy diagram - 12 hour cycle

