



Actinic BL TL(-K) / TL-D(-K)

ACTINIC BL 6W/10 FAM/10X25BOX

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G5
Life to 50% Failures (Nom)	10,000 hour(s)
Useful Life (Nom)	5,000 hour(s)
Light Technical	
Color Code	10
Color Designation	Actinic
Chromaticity Coordinate X (Nom)	222
Chromaticity Coordinate Y (Nom)	210


UV Depreciation at 1000 h	25 %
UV Depreciation at 2000 h	35 %
UV Depreciation at 5000 h	50 %
UV Depreciation at 500 h	17 %
UV Depreciation at 8000 h	60 %
Operating and Electrical	
Power Consumption	6 W
Lamp Current (Nom)	0.16 A

Actinic BL TL(-K) / TL-D(-K)

Voltage (Nom)	42 V
Mechanical and Housing	
Bulb Shape	T16
Net Weight (Piece)	0.046 lb
Approval and Application	
Mercury (Hg) Content (Nom)	4.4 mg
CE mark	Yes
UV	
UV-A Radiation 100Hr (IEC)	1.4 W


Product Data	
Order product name	Actinic BL TL 6W/10 1FM/10X25CC
Full product name	ACTINIC BL 6W/10 FAM/10X25BOX
Full product code	871150026039027
Order code	258954
Material Nr. (12NC)	928000501030
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500260390
Numerator - Packs per outer box	250
EAN/UPC - Case	8711500260413

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
Actinic BL TL 6W/10 1FM/ 10X25CC	5/8 inch	8-3/8 inch	8-5/8 inch	8-9/16 inch	8-15/16 inch

Photometric data



Spectral Power Distribution Colour - Actinic BL TL 6W/10 1FM/10X25CC

Actinic BL TL(-K) / TL-D(-K)

