



TL Mini Standard Colours



TL Mini EL 6W/33-640 FAM/10X25BOX

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (nom.)	
Cap base	G5	42 V	
Flux measurement reference	Sphere	Controls and Dimming	
Life to 50% failures (nom.)	10,000 h	Dimmable	Yes
Light Technical		Mechanical and Housing	
Colour Code	33-640	Bulb shape	T5
Luminous Flux	260 lm	Net Weight (Piece)	21.000 g
Colour designation	Cool White (CW)	Approval and Application	
Chromaticity Coordinate X (Nom)	0.38	Energy Efficiency Class	G
Chromaticity Coordinate Y (Nom)	0.38	Mercury (Hg) content (max.)	2.5 mg
Correlated Colour Temperature (Nom)	4000 K	Mercury (Hg) content (nom.)	4.4 mg
Luminous efficacy (rated) (nom.)	43 lm/W	Energy consumption kWh/1,000 hours	6 kWh
Colour rendering index (CRI)	59	EPREL Registration Number	423488
Operating and Electrical		Product Data	
Power Consumption	6.0 W	Order product name	TL Mini EL 6W/33-640 FAM/10X25BOX
Lamp current (nom.)	0.160 A	Full product name	TL Mini EL 6W/33-640 FAM/10X25BOX

TL Mini Standard Colours

Full EOC	871150071583827
Order code	928000503340
Material no. (12 NC)	928000503340
Local order code	633
Numerator – quantity per pack	1


EAN/UPC – Product/Case	8711500715838
Numerator – packs per outer box	250
EAN/UPC – Case	8711500715852

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini EL 6W/33-640 FAM/10X25BOX	16 mm	212.1 mm	219.2 mm	216.8 mm	226.3 mm

Photometric data



Spectral Power Distribution Colour – TL Mini EL 6W/33-640 FAM/10X25BOX

