



TL Mini Blacklight Blue

F6T5/BLB (TL6W/108) LEAD FREE

This TL Miniature lamp (tube diameter 16 mm) is made of blacklight blue (dark blue) glass, which transmits UV-A radiation, but gives only a minimum of visible light. It is a perfect solution for quick detection of UV-reflecting materials. It is used especially for testing, inspection and analysis in various branches of industry, e.g. criminology, philately and medicine. Furthermore, it is applied to create special effects in the entertainment industry, e.g. in nightclubs and theaters.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G5
Life to 50% Failures (Nom)	8,000 hour(s)
Light Technical	
Color Code	108 [08 lead free glass]
Color Designation	Blacklight Blue
Operating and Electrical	
Power Consumption	6.0 W
Lamp Current (Nom)	0.170 A


Voltage (Nom)	42 V
Mechanical and Housing	
Bulb Shape	T5
Net Weight (Piece)	0.054 lb
Approval and Application	
CE mark	Yes
Product Data	
Order product name	TL 6W BLB 1FM/10X25CC

TL Mini Blacklight Blue

Full product name	F6T5/BLB (TL6W/108) LEAD FREE
Full product code	871150095098727
Order code	157552
Material Nr. (12NC)	928000510803
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8711500950987
Numerator - Packs per outer box	250
EAN/UPC - Case	8711500950970

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 6W BLB 1FM/10X25CC	5/8 inch	8-3/8 inch	8-5/8 inch	8-9/16 inch	8-15/16 inch

Photometric data



Spectral Power Distribution Colour - TL 6W BLB 1FM/10X25CC

