



T5 Preheat

F8T5/CW PH 25PK

Philips T5 Fluorescent Lamps are incredibly powerful, environmentally responsible, long life lamps with an ultra-slim profile. This translates into reduced maintenance and disposal costs and also allows the use of smaller fixtures—which reduces ceiling clutter.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information		Controls and Dimming	
Cap-Base	G5	Dimmable	Yes
Life to 50% Failures (Nom)	10,000 hour(s)		
Light Technical		Mechanical and Housing	
Color Code	33-640	Bulb Shape	T5
Luminous Flux	410 lm	Net Weight (Piece)	0.06 lb
Color Designation	Cool White (CW)		
Correlated Color Temperature (Nom)	4100 K	Approval and Application	
Luminous Efficacy (rated) (Nom)	51 lm/W	Mercury (Hg) Content (Nom)	4.4 mg
Color rendering index (CRI)	60	Energy Consumption kWh/1000 h	8 kWh
Operating and Electrical		Product Data	
Power Consumption	7.1 W	Order product name	F8T5/CW PH 25PK
Lamp Current (Nom)	0.145 A	Full product name	F8T5/CW PH 25PK
Voltage (Nom)	56 V	Order code	332478
		Material Nr. (12NC)	928001003321
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	046677114640

T5 Preheat


Numerator - Packs per outer box	25
EAN/UPC - Case	50046677114645

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
F8T5/CW PH 25PK	5/8 inch	11-3/8 inch	11-5/8 inch	11-9/16 inch	11-15/16 inch

Photometric data



Spectral Power Distribution Colour - F8T5/CW PH 25PK

