



Flexo Print

TL 60W/10R

Flexo print TL lamps emit almost all of their light (99.9%) in the useful UVA and visible blue wavebands – between 350 and 400 nm – and have peak intensity at 370 nm (except for the /03 version). This makes them ideal for flexo printing equipment and photopolymerization processes. In addition, the ‘R’ lamps in the family have an internal 200-degree reflector to further optimize the lamp’s overall efficiency.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		UV Depreciation at 500 h	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	10 %	
Life to 50% Failures (Nom)	2,000 hour(s)	Operating and Electrical	
Useful Life (Nom)	1,000 hour(s)	Power Consumption	62 W
Light Technical		Lamp Current (Nom)	0.7 A
Color Code	10-R	Voltage (Nom)	102 V
Color Designation	Ultra Violet A	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	222	Bulb Shape	T38
Chromaticity Coordinate Y (Nom)	210	Net Weight (Piece)	0.574 lb
UV Depreciation at 1000 h	15 %	Approval and Application	
UV Depreciation at 2000 h	30 %	Mercury (Hg) Content (Nom)	13.0 mg


Flexo Print

CE mark	Yes
UV	
UV-A Radiation 100Hr (IEC)	15.8 W
Product Data	
Order product name	TL 60W/10-R SLV/25
Full product name	TL 60W/10R
Full product code	871150061572540


Order code	261693
Material Nr. (12NC)	928008401003
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500615725
Numerator - Packs per outer box	25
EAN/UPC - Case	8711500615732

Dimensional drawing

Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL 60W/10-R SLV/25	1-5/8 inch	47-1/4 inch	47-1/2 inch	47-7/16 inch	47-13/16 inch



Photometric data



Spectral Power Distribution Colour - TL 60W/10-R SLV/25

