



TL-E LIFEMAX

Standard Colours

32 W G10q Cool daylight Circular fluorescent

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes where color rendering is not important.


Product data

| General Information | |
|------------------------------------|----------------|
| Cap-Base | G10q |
| Nominal lifetime | 8,000 hour(s) |
| Life to 50% Failures (Nom) | 13,000 hour(s) |
| Light Technical | |
| Color Code | 54-765 |
| Luminous Flux | 1,750 lm |
| Color Designation | Cool Daylight |
| Correlated Color Temperature (Nom) | 6200 K |
| Luminous Efficacy (rated) (Nom) | 57 lm/W |
| Color rendering index (CRI) | 72 |
| Operating and Electrical | |
| Power Consumption | 32.0 W |
| Lamp Current (Nom) | 0.450 A |
| Voltage (Nom) | 81 V |
| Controls and Dimming | |
| Dimmable | Yes |

| Mechanical and Housing | |
|---------------------------------|--|
| Bulb Shape | C-T29 |
| Net Weight (Piece) | 0.180 kg |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 9 mg |
| Product Data | |
| Order product name | 32 W G10q Cool daylight Circular fluorescent |
| Full product name | 32 W G10q Cool daylight Circular fluorescent |
| Full product code | 871150063387301 |
| Order code | 928026305436 |
| Material Nr. (12NC) | 928026305436 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8711500633873 |
| Numerator - Packs per outer box | 20 |
| EAN/UPC - Case | 8711500633880 |


TL-E LIFEMAX Standard Colours

Dimensional drawing



| Product | D (max) | D (min) | E (min) | E (max) | I (min) | I (max) |
|--|---------|---------|----------|----------|----------|----------|
| 32 W G10q Cool daylight Circular fluorescent | 30.9 mm | 27.1 mm | 299.0 mm | 303.5 mm | 241.0 mm | 246.0 mm |

Photometric data



Spectral Power Distribution Colour - TL-E 32W/54-765 1CT/20

