



MASTER TL-E Circular Super 80

32 W G10q Cool daylight Circular fluorescent

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)	
Cap-Base	G10q	81 V	
Nominal lifetime	8,000 h	Controls and Dimming	
Life to 50% Failures (Nom)	13,000 h	Dimmable	Yes
Light Technical		Mechanical and Housing	
Color Code	865 [CCT of 6500K]	Bulb Shape	C-T29
Luminous Flux	2,310 lm	Approval and Application	
Color Designation	Cool Daylight	Mercury (Hg) Content (Nom)	8 mg
Luminous Efficacy (rated) (Nom)	72 lm/W	Energy Consumption kWh/1000 h	35 kWh
Correlated Color Temperature (Nom)	6500 K	Product Data	
Color rendering index (CRI)	80	Order product name	32 W G10q Cool daylight Circular fluorescent
Operating and Electrical		Full product name	32 W G10q Cool daylight Circular fluorescent
Power Consumption	32.0 W	Full product code	871150064038300
Lamp Current (Nom)	0.450 A		

MASTER TL-E Circular Super 80

Local code description	TLE32W865
Order code	928026386574
Material Nr. (12NC)	928026386574
Local order code	TLE32W865
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.110 kg

EAN/UPC - Product/Case	8711500640383
Numerator - Packs per outer box	20
EAN/UPC - Case	8727900813616

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
32 W G10q Cool daylight Circular fluorescent	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

