



MASTER TL-E Circular Super 80

32 W G10q Cool daylight Circular fluorescent

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Voltage (Nom)		81 V
Cap-Base	G10q	Controls and Dimming		
Nominal lifetime	8,000 h	Dimmable	Yes	
Life to 50% Failures (Nom)	13,000 h	Mechanical and Housing		
Light Technical		Bulb Shape	C-T29	
Color Code	865 [CCT of 6500K]	Approval and Application		
Luminous Flux	2,310 lm	Energy Consumption kWh/1000 h	35 kWh	
Color Designation	Cool Daylight	Mercury (Hg) Content (Nom)	8 mg	
Luminous Efficacy (rated) (Nom)	72 lm/W	Product Data		
Correlated Color Temperature (Nom)	6500 K	Order product name	32 W G10q Cool daylight Circular fluorescent	
Color rendering index (CRI)	80	Full product name	32 W G10q Cool daylight Circular fluorescent	
Operating and Electrical		Full product code	871150064038300	
Power Consumption	32.0 W			
Lamp Current (Nom)	0.450 A			

MASTER TL-E Circular Super 80

Local code description	TLE32W865
Order code	928026386574
Material Nr. (12NC)	928026386574
Local order code	TLE32W865
Net Weight (Piece)	0.110 kg

EAN/UPC - Product/Case	8711500640383
Numerator - Packs per outer box	20
EAN/UPC - Case	8727900813616

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
32 W G10q Cool daylight Circular fluorescent	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

