



# MASTER TL-E Circular Super 80

## 32 W G10q Cool daylight Circular fluorescent

This circular TL lamp (tube diameter 29 mm) enables omni-directional light distribution. It is suitable for use in a wide range of luminaires for various purposes, including decorative ones, in 'human' applications such as schools, offices, shops and homes, and for lighting of residential areas.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Voltage (Nom)		Controls and Dimming	
Cap-Base	G10q		81 V		
Nominal lifetime	8,000 hour(s)	<b>Controls and Dimming</b>			
Life to 50% Failures (Nom)	13,000 hour(s)	Dimmable	Yes		
Light Technical		Mechanical and Housing			
Color Code	865 [CCT of 6500K]	Bulb Shape	C-T29		
Luminous Flux	2,310 lm	Net Weight (Piece)	0.110 kg		
Color Designation	Cool Daylight	<b>Approval and Application</b>			
Correlated Color Temperature (Nom)	6500 K	Mercury (Hg) Content (Nom)	8 mg		
Luminous Efficacy (rated) (Nom)	72 lm/W	Energy Consumption kWh/1000 h	35 kWh		
Color rendering index (CRI)	80				
Operating and Electrical		Product Data			
Power Consumption	32.0 W	Order product name	32 W G10q Cool daylight Circular fluorescent		
Lamp Current (Nom)	0.450 A	Full product name	32 W G10q Cool daylight Circular fluorescent		

# MASTER TL-E Circular Super 80

Full product code	871150064038300
Order code	928026386574
Material Nr. (12NC)	928026386574
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8711500640383

Numerator - Packs per outer box	20
EAN/UPC - Case	8727900813616

## Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
32 W G10q Cool daylight Circular fluorescent	30.9 mm	27.1 mm	299.0 mm	303.5 mm	241.0 mm	246.0 mm

