



Circline

22W T9 Daylight Deluxe Circline Fluorescent


T9 4-Pin Circular Fluorescent Lamps.

Product data

General Information	
Cap-Base	G10q
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54
Luminous Flux	910 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	79
Operating and Electrical	
Power Consumption	20.5 W
Lamp Current (Nom)	0.37 A
Voltage (Nom)	61 V
Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	C-T29
Net Weight (Piece)	0.110 kg
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	22W T9 Daylight Deluxe Circline Fluorescent
Full product name	22W T9 Daylight Deluxe Circline Fluorescent
Order code	928028405435
Material Nr. (12NC)	928028405435
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677392352
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677392357

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
22W T9 Daylight Deluxe	31.0 mm	26.2 mm	203.2 mm	215.9 mm	149.1 mm	155.7 mm
Circline Fluorescent						

