



Circline

FC8T9/DAYDLX/22W/8 12PK

T9 4-Pin Circular Fluorescent Lamps.

Warnings and Safety


- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G10q
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54
Luminous Flux	910 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	79
Operating and Electrical	
Power Consumption	20.5 W
Lamp Current (Nom)	0.37 A
Voltage (Nom)	61 V
Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	C-T29
Net Weight (Piece)	0.243 lb
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	22W T9 Daylight Deluxe Circline Fluorescent
Full product name	FC8T9/DAYDLX/22W/8 12PK
Order code	392357
Material Nr. (12NC)	928028405435
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677392352
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677392357

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
22W T9 Daylight	1-1/4 inch	1-1/16 inch	8 inch	8-1/2 inch	5-7/8 inch	6-1/8 inch
Deluxe Circline						
Fluorescent						

