



Circline

22W T9 Bright White Circline Fluorescent


T9 4-Pin Circular Fluorescent Lamps.

Product data

General Information	
Cap-Base	G10q
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	830 [CCT of 3000K]
Luminous Flux	1,150 lm
Color Designation	Bright White
Correlated Color Temperature (Nom)	3000 K
Color rendering index (CRI)	80
Operating and Electrical	
Power Consumption	20.5 W
Lamp Current (Nom)	0.37 A
Voltage (Nom)	61 V
Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	C-T29
Net Weight (Piece)	0.110 kg
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	22W T9 Bright White Circline Fluorescent
Full product name	22W T9 Bright White Circline Fluorescent
Order code	928028483035
Material Nr. (12NC)	928028483035
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677392222
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677392227

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
22W T9 Bright White	31.0 mm	26.2 mm	203.2 mm	215.9 mm	149.1 mm	155.7 mm
Circline Fluorescent						

