



Circline

32W T9 Daylight Deluxe Circline Fluorescent


T9 4-Pin Circular Fluorescent Lamps.

Product data

General Information	
Cap-Base	G10q
Life to 50% Failures (Nom)	13,000 hour(s)
Light Technical	
Color Code	54
Luminous Flux	1,570 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6200 K
Color rendering index (CRI)	79
Operating and Electrical	
Power Consumption	31 W
Lamp Current (Nom)	0.43 A
Voltage (Nom)	84 V
Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Bulb Shape	C-T29
Net Weight (Piece)	0.180 kg
Approval and Application	
Mercury (Hg) Content (Nom)	8.0 mg
Product Data	
Order product name	32W T9 Daylight Deluxe Circline Fluorescent
Full product name	32W T9 Daylight Deluxe Circline Fluorescent
Order code	928028605435
Material Nr. (12NC)	928028605435
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677262600
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677262605

Dimensional drawing



Product	D (max)	D (min)	E (min)	E (max)	I (min)	I (max)
32W T9 Daylight Deluxe	31.0 mm	26.2 mm	292.1 mm	304.8 mm	239.5 mm	246.1 mm
Circline Fluorescent						

