



Circline

40W T9 Cool White Circline Fluorescent


T9 4-Pin Circular Fluorescent Lamps.

Product data

| General Information | |
|------------------------------------|-----------------|
| Cap-Base | G10q |
| Life to 50% Failures (Nom) | 13,000 hour(s) |
| Light Technical | |
| Color Code | 33 |
| Luminous Flux | 2,500 lm |
| Color Designation | Cool White (CW) |
| Correlated Color Temperature (Nom) | 4100 K |
| Color rendering index (CRI) | 62 |
| Operating and Electrical | |
| Power Consumption | 39.5 W |
| Lamp Current (Nom) | 0.42 A |
| Voltage (Nom) | 109 V |
| Controls and Dimming | |
| Dimmable | No |

| Mechanical and Housing | |
|---------------------------------|--|
| Bulb Shape | C-T29 |
| Net Weight (Piece) | 0.250 kg |
| Approval and Application | |
| Mercury (Hg) Content (Nom) | 8.0 mg |
| Product Data | |
| Order product name | 40W T9 Cool White Circline Fluorescent |
| Full product name | 40W T9 Cool White Circline Fluorescent |
| Order code | 928028803335 |
| Material Nr. (12NC) | 928028803335 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 046677391188 |
| Numerator - Packs per outer box | 12 |
| EAN/UPC - Case | 50046677391183 |

Dimensional drawing



| Product | D (max) | D (min) | E (min) | E (max) | I (min) | I (max) |
|----------------------|---------|---------|----------|----------|----------|----------|
| 40W T9 Cool White | 30.9 mm | 27.1 mm | 393.7 mm | 406.4 mm | 341.0 mm | 347.7 mm |
| Circline Fluorescent | | | | | | |

