



TL-X XL



TL-X XL 40W/33-640 SLV/25

Single-pin low-pressure mercury discharge lamps with a tubular 38 mm envelope

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

| General Information | |
|-------------------------------------|-----------------|
| Cap base | FA6 |
| Flux measurement reference | Sphere |
| Life to 50% failures (nom.) | 26,000 h |
| Light Technical | |
| Colour Code | 33-640 |
| Luminous Flux | 2,300 lm |
| Colour designation | Cool White (CW) |
| Chromaticity Coordinate X (Nom) | 0.38 |
| Chromaticity Coordinate Y (Nom) | 0.38 |
| Correlated Colour Temperature (Nom) | 4000 K |
| Luminous efficacy (rated) (nom.) | 58 lm/W |
| Colour rendering index (CRI) | 60 |
| Operating and Electrical | |
| Power Consumption | 40.0 W |
| Lamp current (nom.) | 0.430 A |
| Voltage (nom.) | 103 V |


| Controls and Dimming | |
|------------------------------------|---------------------------|
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb shape | T12 |
| Net Weight (Piece) | 233.000 g |
| Approval and Application | |
| Energy Efficiency Class | G |
| Mercury (Hg) content (max.) | 12 mg |
| Mercury (Hg) content (nom.) | 12.0 mg |
| Energy consumption kWh/1,000 hours | 40 kWh |
| EPREL Registration Number | 423515 |
| Product Data | |
| Order product name | TL-X XL 40W/33-640 SLV/25 |
| Full product name | TL-X XL 40W/33-640 SLV/25 |
| Full EOC | 871150026137340 |
| Order code | 26137340 |
| Material no. (12 NC) | 928037903332 |
| Local order code | TLX4033XL |

TL-X XL

| | |
|---------------------------------|---------------|
| Numerator – quantity per pack | 1 |
| EAN/UPC – Product/Case | 8711500261373 |
| Numerator – packs per outer box | 25 |


| | |
|----------------|---------------|
| EAN/UPC – Case | 8711500261380 |
|----------------|---------------|

Dimensional drawing



| Product | D (max) | A (max) | B (max) | B (min) | C (max) |
|---------------------------|---------|------------|----------|------------|------------|
| TL-X XL 40W/33-640 SLV/25 | 40.5 mm | 1,183.5 mm | 1,202 mm | 1,198.5 mm | 1,220.5 mm |

Photometric data



Spectral Power Distribution Colour – TL-X XL 40W/33-640 SLV/25

