



MASTERColour CDM-R Elite



MASTERColour CDM-R Elite 70W/942 E27 PAR30L 40D

Compact, very high-efficiency, long-life Ceramic Metal Halide discharge reflector lamp producing crisp white sparkling light with high colour rendering

Warnings and Safety

- Use only with electronic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)

Product data

General Information		Operating and Electrical	
Cap base	E27	Colour rendering index (CRI)	92
Operating position	UNIVERSAL [Any or Universal (U)]	LLMF at end of nominal lifetime (nom.)	75 %
Switching Cycle	1,350	Luminous flux in 90° cone (rated)	4,500 lm
Flux measurement reference	Narrow Cone		
Life to 50% failures (nom.)	15,000 h	Operating and Electrical	
		Power Consumption	73.2 W
		Warm-up time to 60% light	120 s
		Voltage (nom.)	90 V
		Controls and Dimming	
		Dimmable	No
		Mechanical and Housing	
		Lamp Finish	Clear
		Bulb shape	PAR30L
		Net Weight (Piece)	0.225 kg

MASTERCcolour CDM-R Elite

Approval and Application


Energy Efficiency Class	G
Mercury (Hg) content (max.)	6.6 mg
Mercury (Hg) content (nom.)	6.5 mg
Energy consumption kWh/1,000 hours	74 kWh
EPREL Registration Number	473306

Product Data

Order product name	MC CDM-R Elite 70W/942 E27 PAR30L 40D
Full product name	MASTERCcolour CDM-R Elite 70W/942 E27 PAR30L 40D



Full EOC	871829165169700
Order code	65169700
Material no. (12 NC)	928053100630
Local order code	70CDMRELP394240
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8718291651697
Numerator – packs per outer box	6
EAN/UPC – Case	8718291651703

Dimensional drawing



Product	D (max)	C (max)
MC CDM-R Elite 70W/942 E27 PAR30L 40D	97 mm	123 mm

Photometric data





Spectral Power Distribution Colour - MC CDM-R Elite 70W/942 E27 PAR30L 40D

Light Distribution Diagram - MC CDM-R Elite 70W/942 E27 PAR30L 40D

MASTERCcolour CDM-R Elite

Lifetime



LDLE_CDM-R-E_0006-Life expectancy diagram

Lumen Maintenance Diagram - MC CDM-R Elite 70W/942 E27 PAR30L 40D

