



MSR

MSR 1200 1CT/3

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	G22
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	800 hour(s)
Light Technical	
Color Code	- [Not Specified]
Luminous Flux	103,000 lm
Chromaticity Coordinate X (Nom)	325
Chromaticity Coordinate Y (Nom)	327
Correlated Color Temperature (Nom)	5900 K
Luminous Efficacy (rated) (Nom)	88 lm/W

Color rendering index (CRI)	80
Arc Length O (Nom)	10.0 mm
Operating and Electrical	
Power Consumption	1,200 W
Lamp Current (Nom)	13.8 A
Controls and Dimming	
Dimmable	No

Mechanical and Housing

Net Weight (Piece)	0.331 lb
--------------------	----------

Approval and Application

CE mark	Yes
---------	-----

Product Data

Order product name	MSR 1200 1CT/3
--------------------	----------------

Full product name	MSR 1200 1CT/3
-------------------	----------------

Full product code	872790091121300
-------------------	-----------------

Order code	245514
------------	--------


Material Nr. (12NC)	928078105114
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---


EAN/UPC - Product/Case	8727900911213
------------------------	---------------

Numerator - Packs per outer box	3
---------------------------------	---

EAN/UPC - Case	8727900911220
----------------	---------------

Dimensional drawing

Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR 1200	1-5/8	7/16	3-5/16	3-7/16	3-3/8	6-15/16	2-1/8
1CT/3	inch	inch	inch	inch	inch	inch	inch

Photometric data

Spectral Power Distribution Colour - MSR 1200 1CT/3

