



MASTERColour CDM-TD



MASTERC CDM-TD 70W/830 RX7s 1CT/12

Range of double-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	RX7s
Operating position	P45 [Parallel +/-45D or Horizontal(HOR)]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	16,000 h

Light Technical	
Colour Code	830 [CCT of 3000K]
Luminous Flux	6,000 lm
Colour designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.434
Chromaticity Coordinate Y (Nom)	0.398
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	85 lm/W

Colour rendering index (CRI)	80
Arc Length O (Nom)	8 mm

Operating and Electrical	
Power Consumption	71.0 W
Voltage (nom.)	94 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T22

MASTERC colour CDM-TD


Net Weight (Piece)	21.000 g
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	3.4 mg
Mercury (Hg) content (nom.)	3.4 mg
Energy consumption kWh/1,000 hours	71 kWh
EPREL Registration Number	473326
CE mark	Yes

Full product name	MASTERC CDM-TD 70W/830 RX7s 1CT/12
Full EOC	871150019782515
Order code	928082205125
Material no. (12 NC)	928082205125
Local order code	70CDMTD830
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500197825
Numerator – packs per outer box	12
EAN/UPC – Case	8711500197832

Product Data



Order product name	MASTERC CDM-TD 70W/830 RX7s 1CT/12
--------------------	------------------------------------

Dimensional drawing



Product	D (max)	D O	C (max)
MASTERC CDM-TD 70W/830 RX7s 1CT/12	22 mm	8 mm	119.63 mm

Photometric data





Light Distribution Diagram - MASTERC CDM-TD 70W/830 RX7s 1CT/12

Spectral Power Distribution Colour - MASTERC CDM-TD 70W/830 RX7s 1CT/12

MASTERC colour CDM-TD

Lifetime



LDLE_CDM-TD_0001-Life expectancy diagram

Lumen Maintenance Diagram - MASTER CDM-TD 70W/830 RX7s 1CT/12

