



MASTERColour CDM-TD



MASTERC CDM-TD 150W/830 RX7s 1CT

Range of double-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Lamps may use electronic or electromagnetic control gear
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	RX7s
Operating position	P45 [Parallel +/-45D or Horizontal(HOR)]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	16,000 h

Light Technical	
Colour Code	830 [CCT of 3000K]
Luminous Flux	12,750 lm
Colour designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.434
Chromaticity Coordinate Y (Nom)	0.398
Correlated Colour Temperature (Nom)	3000 K
Luminous efficacy (rated) (nom.)	87 lm/W

Colour rendering index (CRI)	88
Arc Length O (Nom)	10 mm

Operating and Electrical	
Power Consumption	147.0 W
Voltage (nom.)	98 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Lamp Finish	Clear
Bulb shape	T22

MASTERC colour CDM-TD


Net Weight (Piece)	26.700 g
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	10.2 mg
Mercury (Hg) content (nom.)	10.23 mg
Energy consumption kWh/1,000 hours	147 kWh
EPREL Registration Number	473334
CE mark	Yes

Product Data

Order product name	MASTERC CDM-TD 150W/830 RX7s 1CT
--------------------	----------------------------------


Full product name	MASTERC CDM-TD 150W/830 RX7s 1CT
Full EOC	871150019784915
Order code	928083605133
Material no. (12 NC)	928083605133
Local order code	150CDMTD830
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500197849
Numerator – packs per outer box	12
EAN/UPC – Case	8711500197856

Dimensional drawing




Product	D (max)	D O	C (max)
MASTERC CDM-TD 150W/830 RX7s 1CT	22 mm	10 mm	137.43 mm

Photometric data





Light Distribution Diagram - MASTERC CDM-TD 150W/830 RX7s 1CT



Spectral Power Distribution Colour - MASTERC CDM-TD 150W/830 RX7s 1CT

MASTERC colour CDM-TD

Lifetime



LDLE_CDM-TD_0001-Life expectancy diagram

Lumen Maintenance Diagram - MASTER CDM-TD 150W/830 RX7s 1CT

