



MasterColor CDM-T T6

MasterColor CDM-T 70W/942 G12 T6 CL

MasterColor CDM lamp gives a unique combination of unbeatable light quality and consistent performance over lifetime while keeping running costs low. The Philips MasterColor Tubular Single-Ended T6 lamp is a compact, energy efficient, ceramic metal halide lamp that provides crisp, sparkling light.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	G12	85 lm/W	
Operating Position	UNIVERSAL [Any or Universal (U)]	Color rendering index (CRI)	
Life to 50% Failures (Nom)	12,000 hour(s)	92	
Light Technical		Arc Length O (Nom)	
Color Code	942 [CCT of 4200K]	6 mm	
Color Designation	Cool White (CW)	Operating and Electrical	
Chromaticity Coordinate X (Nom)	0.377	Power Consumption	
Chromaticity Coordinate Y (Nom)	0.376	73.2 W	
Correlated Color Temperature (Nom)	4200 K	Voltage (Nom)	
		88 V	
		Controls and Dimming	
		Dimmable	
		No	

MasterColor CDM-T T6

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	T19
Net Weight (Piece)	0.064 lb
Approval and Application	
Mercury (Hg) Content (Nom)	6.1 mg
Energy Consumption kWh/1000 h	80 kWh
Product Data	
Order product name	CDM-T 70W/942 G12 T6 CL


Full product name	MasterColor CDM-T 70W/942 G12 T6 CL
Order code	281378
Material Nr. (12NC)	928084505115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677281373
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677281378

Dimensional drawing




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
CDM-T	13/16	0.75	1/4	2-3/16	2-1/4	2-1/4	4-1/16
70W/942 G12	inch	inch	inch	inch	inch	inch	inch
T6 CL							

Photometric data




Spectral Power Distribution Colour - CDM-T 70W/942 G12 T6 CL




Light Distribution Diagram - CDM-T 70W/942 G12 T6 CL

MasterColor CDM-T T6

Lifetime



LDLE_CDM-T_70W_942-Life expectancy diagram



Lumen Maintenance Diagram - CDM-T 70W/942 G12 T6 CL

