



MASTERColour CDM-T



MASTERC CDM-T 70W/942 G12 1CT/12

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information		Luminous efficacy (rated) (nom.)	
Cap base	G12	85 lm/W	
Operating position	UNIVERSAL [Any or Universal (U)]	Colour rendering index (CRI)	
Flux measurement reference	Sphere	92	
Life to 50% failures (nom.)	12,000 h	Arc Length O (Nom)	
Light Technical		6 mm	
Colour Code	942 [CCT of 4200K]	Operating and Electrical	
Luminous Flux	6,200 lm	Power Consumption	
Colour designation	Cool White (CW)	73.2 W	
Chromaticity Coordinate X (Nom)	0.371	Voltage (nom.)	
Chromaticity Coordinate Y (Nom)	0.366	88 V	
Correlated Colour Temperature (Nom)	4200 K	Controls and Dimming	
		Dimmable	
		No	
		Mechanical and Housing	
		Lamp Finish	
		Clear	

MASTERC colour CDM-T


Bulb shape	T19
Net Weight (Piece)	0.029 kg
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	6.1 mg
Mercury (Hg) content (nom.)	6.1 mg
Energy consumption kWh/1,000 hours	74 kWh
EPREL Registration Number	473337
CE mark	Yes

Product Data

Order product name	MASTERC CDM-T 70W/942 G12 1CT/12
--------------------	----------------------------------


Full product name	MASTERC CDM-T 70W/942 G12 1CT/12
Full EOC	871150019927015
Order code	928084505131
Material no. (12 NC)	928084505131
Local order code	70CDMT942
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500199270
Numerator – packs per outer box	12
EAN/UPC – Case	8711500199287

Dimensional drawing




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 70W/942	20 mm	0.75 in	6 mm	55 mm	57 mm	56 mm	103 mm
G12 1CT/12							

Photometric data




Spectral Power Distribution Colour - MASTERC CDM-T 70W/942 G12 1CT/12




Light Distribution Diagram - MASTERC CDM-T 70W/942 G12 1CT/12

MASTERC colour CDM-T

Lifetime



LDLE_CDM-T_70W_942-Life expectancy diagram



Lumen Maintenance Diagram - MASTERC CDM-T 70W/942 G12 1CT/12

