



# MASTERColour CDM-T



## MASTERC CDM-T 150W/942 G12 1CT

Range of single-ended, compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

### Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Lamps may use electronic or electromagnetic control gear, except 35W/942 and 20W lamps, which must use electronic control gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data

General Information	
Cap base	G12
Operating position	UNIVERSAL [Any or Universal (U)]
Flux measurement reference	Sphere
Life to 50% failures (nom.)	12,000 h

Light Technical	
Colour Code	942 [CCT of 4200K]
Luminous Flux	12,100 lm
Colour designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.371
Chromaticity Coordinate Y (Nom)	0.366
Correlated Colour Temperature (Nom)	4200 K

Luminous efficacy (rated) (nom.)	82 lm/W
Colour rendering index (CRI)	96
Arc Length O (Nom)	8 mm

Operating and Electrical	
Power Consumption	150.1 W
Voltage (nom.)	90 V

Controls and Dimming	
Dimmable	No

Mechanical and Housing	
Lamp Finish	Clear

# MASTERC colour CDM-T


Bulb shape	T19
Net Weight (Piece)	0.033 kg
<b>Approval and Application</b>	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	10.4 mg
Mercury (Hg) content (nom.)	10.4 mg
Energy consumption kWh/1,000 hours	151 kWh
EPREL Registration Number	473338
CE mark	Yes

## Product Data

Order product name	MASTERC CDM-T 150W/942 G12 1CT
--------------------	--------------------------------


Full product name	MASTERC CDM-T 150W/942 G12 1CT
Full EOC	871150020005115
Order code	928084605131
Material no. (12 NC)	928084605131
Local order code	150CDMT942
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500200051
Numerator – packs per outer box	12
EAN/UPC – Case	8711500200068

## Dimensional drawing




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-T 150W/942 G12 1CT	20 mm	0.75 in	8 mm	55 mm	57 mm	56 mm	110 mm

## Photometric data





Spectral Power Distribution Colour - MASTERC CDM-T 150W/942 G12 1CT



Light Distribution Diagram - MASTERC CDM-T 150W/942 G12 1CT

# MASTERC colour CDM-T

## Lifetime



LDLE\_CDM-T\_150W\_942-Life expectancy diagram

Lumen Maintenance Diagram - MASTERC CDM-T 150W/942 G12 1CT

