



MasterColor CDM-TC T4

MasterColor CDM-TC 70W/830 G8.5 T4 CL

MasterColor CDM lamp gives a unique combination of unbeatable light quality and consistent performance over lifetime while keeping running costs low. The Philips MasterColor Tubular Single-Ended T4 lamp is a compact, energy efficient, ceramic metal halide lamp that provides crisp, sparkling light.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information		Luminous Efficacy (rated) (Nom)	
Cap-Base	G8.5		86 lm/W
Operating Position	UNIVERSAL [Any or Universal (U)]	Color rendering index (CRI)	83
Life to 50% Failures (Nom)	12,000 hour(s)	Arc Length O (Nom)	7 mm
Light Technical		Operating and Electrical	
Color Code	830 [CCT of 3000K]	Power Consumption	73.2 W
Color Designation	Warm White (WW)	Voltage (Nom)	83 V
Chromaticity Coordinate X (Nom)	0.439	Controls and Dimming	
Chromaticity Coordinate Y (Nom)	0.398	Dimmable	No
Correlated Color Temperature (Nom)	3000 K		

MasterColor CDM-TC T4

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	UV-Block Quartz
Bulb Shape	T14
Net Weight (Piece)	0.022 lb
Approval and Application	
Mercury (Hg) Content (Nom)	4.6 mg
Energy Consumption kWh/1000 h	80 kWh
Product Data	
Order product name	CDM-TC 70W/830 G8.5 T4 CL


Full product name	MasterColor CDM-TC 70W/830 G8.5 T4 CL
Order code	373738
Material Nr. (12NC)	928086505115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677373733
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677373738

Dimensional drawing




Product	D (max)	D	O	L (min)	L (max)	L	C (max)
CDM-TC	5/8 inch	0.5	5/16	2-1/16	2-1/8	2-1/16	3-3/8
70W/830 G8.5		inch	inch	inch	inch	inch	inch
T4 CL							

Photometric data




Light Distribution Diagram - CDM-TC 70W/830 G8.5 T4 CL




Spectral Power Distribution Colour - CDM-TC 70W/830 G8.5 T4 CL

MasterColor CDM-TC T4

Lifetime



Lumen Maintenance Diagram - CDM-TC 70W/830 G8.5 T4 CL



LDLE_CDM-TC_0001-Life expectancy diagram

