



MASTERColour CDM-TC



MASTERColour CDM-TC 35W/842 G8.5 1CT/12

Range of single-ended, very compact, high-efficiency, discharge lamps with a stable colour over lifetime and a crisp, sparkling light

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- Control gear must include end-of-life protection (IEC61167, IEC 62035)
- Use only with electronic control gear. 35W/830 lamps may also use electromagnetic gear.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Colour rendering index (CRI)	
Cap base	G8.5		85
Operating position	UNIVERSAL [Any or Universal (U)]	Arc Length O (Nom)	5 mm
Flux measurement reference	Sphere	Operating and Electrical	
Life to 50% failures (nom.)	12,000 h	Power Consumption	39.1 W
Light Technical		Voltage (nom.)	85 V
Colour Code	842 [CCT of 4200K]	Controls and Dimming	
Luminous Flux	3,100 lm	Dimmable	No
Colour designation	Cool White (CW)	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	0.371	Lamp Finish	Clear
Chromaticity Coordinate Y (Nom)	0.366	Bulb material	UV-Block Quartz
Correlated Colour Temperature (Nom)	4200 K	Bulb shape	T14
Luminous efficacy (rated) (nom.)	79 lm/W		

MASTERCoulour CDM-TC

Net Weight (Piece)	10.000 g
Approval and Application	
Energy Efficiency Class	G
Mercury (Hg) content (max.)	2.7 mg
Mercury (Hg) content (nom.)	2.7 mg
Energy consumption kWh/1,000 hours	40 kWh
EPREL Registration Number	473352
Product Data	
Order product name	MASTERC CDM-TC 35W/842 G8.5 1CT/12


Full product name	MASTERCoulour CDM-TC 35W/842 G8.5 1CT/12
Full EOC	871150020957315
Order code	20957315
Material no. (12 NC)	928093805125
Local order code	35CDMTC942
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500209573
Numerator – packs per outer box	12
EAN/UPC – Case	8711500209580

Dimensional drawing



Product	D (max)	D	O	L (min)	L (max)	L	C (max)
MASTERC CDM-TC 35W/842 G8.5 1CT/12	15 mm	0.5 in	5 mm	51 mm	53 mm	52 mm	85 mm


Photometric data



Spectral Power Distribution Colour - MASTERC CDM-TC 35W/842 G8.5 1CT/12

MASTERColour CDM-TC

Lifetime



LDLE_CDM-TC_0001-Life expectancy diagram

