



# MSR Gold™ FastFit

## MSR Gold™ 2000/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 2000/2 FastFit can be operated in a lamp wattage range between 800W and 1400W.

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

| General Information             |                                  |
|---------------------------------|----------------------------------|
| Cap-Base                        | PGJX50                           |
| Operating Position              | UNIVERSAL [Any or Universal (U)] |
| Life to 50% Failures (Nom)      | 750 hour(s)                      |
| Light Technical                 |                                  |
| Color Code                      | 2                                |
| Luminous Flux                   | 157,000 lm                       |
| Chromaticity Coordinate X (Nom) | 297                              |
| Chromaticity Coordinate Y (Nom) | 322                              |

| Correlated Color Temperature (Nom) | 7500 K  |
|------------------------------------|---------|
| Luminous Efficacy (rated) (Nom)    | 78 lm/W |
| Color rendering index (CRI)        | 88      |
| Arc Length O (Nom)                 | 8.0 mm  |
| Operating and Electrical           |         |
| Power Consumption                  | 2,000 W |
| Lamp Current (Nom)                 | 15.4 A  |

## MSR Gold™ FastFit

### Controls and Dimming

|          |     |
|----------|-----|
| Dimmable | Yes |
|----------|-----|

### Mechanical and Housing

|                    |      |
|--------------------|------|
| Net Weight (Piece) | 0 lb |
|--------------------|------|

### Product Data

|                    |                                |
|--------------------|--------------------------------|
| Order product name | MSR Gold 2000/2 FastFit 1CT/8  |
| Full product name  | MSR Gold™ 2000/2 FastFit 1CT/8 |

|                   |                 |
|-------------------|-----------------|
| Full product code | 872790090830500 |
|-------------------|-----------------|

|            |        |
|------------|--------|
| Order code | 245605 |
|------------|--------|

|                     |              |
|---------------------|--------------|
| Material Nr. (12NC) | 928106105114 |
|---------------------|--------------|


|                               |   |
|-------------------------------|---|
| Numerator - Quantity Per Pack | 1 |
|-------------------------------|---|

|                        |               |
|------------------------|---------------|
| EAN/UPC - Product/Case | 8727900908305 |
|------------------------|---------------|

|                                 |   |
|---------------------------------|---|
| Numerator - Packs per outer box | 8 |
|---------------------------------|---|

|                |               |
|----------------|---------------|
| EAN/UPC - Case | 8727900908312 |
|----------------|---------------|

### Dimensional drawing



| Product       | D (max) | O    | L (min) | L (max) | L       | C (max) | F      |
|---------------|---------|------|---------|---------|---------|---------|--------|
| MSR Gold      | 1-3/8   | 5/16 | 2-5/8   | 2-11/16 | 2-11/16 | 5-5/16  | 2 inch |
| 2000/2        | inch    | inch | inch    | inch    | inch    | inch    |        |
| FastFit 1CT/8 |         |      |         |         |         |         |        |

