



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 1000 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information			
Cap-Base	PGJX36	Chromaticity Coordinate X (Nom)	0.321
Operating Position	UNIVERSAL [Any or Universal (U)]	Chromaticity Coordinate Y (Nom)	0.330
Life to 50% Failures (Nom)	900 hour(s)	Correlated Color Temperature (Nom)	6000 K
		Luminous Efficacy (rated) (Nom)	79.3 lm/W
		Color rendering index (CRI)	80
		Arc Length O (Nom)	5.5 mm
Light Technical			
Color Code	- [Not Specified]		
Luminous Flux	79,300 lm		

MSR Gold™ MiniFastFit (Touring/Stage)

Operating and Electrical

Power Consumption	1,000 W
Lamp Current (Nom)	11.4 A

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Net Weight (Piece)	0.121 lb
--------------------	----------


Approval and Application

CE mark	Yes
---------	-----

Product Data

Order product name	MSR Gold 1000 MiniFastFit 1CT/4
Full product name	MSR Gold™ 1000 MiniFastFit 1CT/4
Full product code	871829178508800
Order code	260471
Material Nr. (12NC)	928171405115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291785088
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291785095

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L (max)	C (max)	F (max)	F	F (min)
MSR Gold 1000 MiniFastFit 1CT/4	1-1/16 inch	1/4 inch	2-3/16 inch	2-1/4 inch	2-1/4 inch	4-7/16 inch	1-7/16 inch	1-7/16 inch	1-7/16 inch

