



MSR

MSR 700/2 1CT/8

The high color rendering index of the single ended MSR series ensures that everyone in the audience can enjoy the true colors of the scenery, the stage props, the players and their costumes – in fact everything that is on stage can be made bright and vivid in daylight quality light. Also, thanks to the single ended lamp concept, the luminaire has optimal light collection and direction possibilities to help ensure brightness on stage exactly where and when it is needed. In addition, the MSR can be used in any burning position for easy set-up and convenience.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information		Color rendering index (CRI)		80
Cap-Base	G22	Arc Length O (Nom)		8.0 mm
Operating Position	UNIVERSAL [Any or Universal (U)]			
Life to 50% Failures (Nom)	1,000 hour(s)			
Light Technical				
Color Code	2			
Luminous Flux	55,000 lm			
Chromaticity Coordinate X (Nom)	302			
Chromaticity Coordinate Y (Nom)	320			
Correlated Color Temperature (Nom)	7200 K			
Luminous Efficacy (rated) (Nom)	78 lm/W			
Operating and Electrical				
Power Consumption		700 W		
Lamp Current (Nom)		11 A		
Controls and Dimming				
Dimmable		No		

Mechanical and Housing

Net Weight (Piece)	0.265 lb
--------------------	----------

Approval and Application

CE mark	Yes
---------	-----

Product Data

Order product name	MSR 700/2 1CT/8
--------------------	-----------------

Full product name	MSR 700/2 1CT/8
-------------------	-----------------

Full product code	872790091638600
-------------------	-----------------

Order code	245431
------------	--------


Material Nr. (12NC)	928171505114
---------------------	--------------

Numerator - Quantity Per Pack	1
-------------------------------	---


EAN/UPC - Product/Case	8727900916386
------------------------	---------------

Numerator - Packs per outer box	8
---------------------------------	---

EAN/UPC - Case	8727900916393
----------------	---------------

Dimensional drawing

Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR 700/2 1CT/8	1-3/16 inch	5/16 inch	2-15/16 inch	3 inch	3 inch	6 inch	1-11/16 inch

Photometric data

Spectral Power Distribution Colour - MSR 700/2 1CT/8

