



MSR Gold™ FastFit

MSR Gold™ 2000 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 2000 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	PGJX50
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	750 hour(s)
Light Technical	
Color Code	- [Not Specified]
Luminous Flux (Min)	162,000 lm
Luminous Flux	180,000 lm
Chromaticity Coordinate X (Nom)	321

Chromaticity Coordinate Y (Nom)	332
Correlated Color Temperature (Nom)	6050 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color rendering index (CRI)	91
Arc Length O (Nom)	8.0 mm
Operating and Electrical	
Power Consumption	2,000 W
Lamp Current (Nom)	15.2 A

MSR Gold™ FastFit

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Net Weight (Piece)	0.324 lb
--------------------	----------

Approval and Application


CE mark	Yes
---------	-----

Product Data

Order product name	MSR Gold 2000 FastFit 1CT/8
--------------------	-----------------------------

Full product name	MSR Gold™ 2000 FastFit 1CT/8
Full product code	872790091949300
Order code	245738
Material Nr. (12NC)	928176905114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8727900919493
Numerator - Packs per outer box	8
EAN/UPC - Case	8727900919509

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold	1-3/8	5/16	2-5/8	2-11/16	2-11/16	5-5/16	2 inch
2000 FastFit	inch	inch	inch	inch	inch	inch	
1CT/8							

