



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 575/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information			
Cap-Base	PGJX28	Chromaticity Coordinate X (Nom)	296
Operating Position	UNIVERSAL [Any or Universal (U)]	Chromaticity Coordinate Y (Nom)	315
Life to 50% Failures (Nom)	750 hour(s)	Correlated Color Temperature (Nom)	7500 K
		Luminous Efficacy (rated) (Nom)	61.5 lm/W
		Color rendering index (CRI)	70
		Arc Length O (Nom)	3.5 mm
Light Technical			
Color Code	2		
Luminous Flux	35,500 lm		

MSR Gold™ MiniFastFit (Touring/Stage)

Operating and Electrical	
Power Consumption	575 W
Lamp Current (Nom)	10.2 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Net Weight (Piece)	0.154 lb
Approval and Application	
CE mark	Yes


Product Data	
Order product name	MSR Gold 575/2 MiniFastFit 1CT/4
Full product name	MSR Gold™ 575/2 MiniFastFit 1CT/4
Full product code	871829122109800
Order code	287201
Material Nr. (12NC)	928184005115
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291221098
Numerator - Packs per outer box	4
EAN/UPC - Case	8718291221104

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold 575/2 MiniFastFit 1CT/4	15/16 inch	3/16 inch	2-3/16 inch	2-1/4 inch	2-1/4 inch	4-7/16 inch	1-7/16 inch	1-7/16 inch	1-7/16 inch

Photometric data



Spectral Power Distribution Colour - MSR Gold 575/2 MiniFastFit 1CT/4

MSR Gold™ MiniFastFit (Touring/Stage)

