



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 700 MiniFastFit 1CT/16

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information			
Cap-Base	PGJX28	Chromaticity Coordinate X (Nom)	289
Operating Position	UNIVERSAL [Any or Universal (U)]	Chromaticity Coordinate Y (Nom)	308
Life to 50% Failures (Nom)	750 hour(s)	Correlated Color Temperature (Nom)	6000 K
		Luminous Efficacy (rated) (Nom)	68.5 lm/W
		Color rendering index (CRI)	72
		Arc Length O (Nom)	3.5 mm
Light Technical			
Color Code	- [Not Specified]		
Luminous Flux	48,000 lm		

MSR Gold™ MiniFastFit (Touring/Stage)

Operating and Electrical

Power Consumption	700 W
Lamp Current (Nom)	10.8 A

Controls and Dimming

Dimmable	Yes
----------	-----

Mechanical and Housing

Net Weight (Piece)	0.117 lb
--------------------	----------


Approval and Application

CE mark	Yes
---------	-----

Product Data

Order product name	MSR Gold 700 MiniFastFit 1CT/16
Full product name	MSR Gold™ 700 MiniFastFit 1CT/16
Full product code	871829114103700
Order code	277095
Material Nr. (12NC)	928194105114
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718291141037
Numerator - Packs per outer box	16
EAN/UPC - Case	8718291141044

Dimensional drawing



Product	D (max)	O	L (min)	L (max)	L	C (max)	F (max)	F	F (min)
MSR Gold 700 MiniFastFit 1CT/16	15/16 inch	3/16 inch	2-3/16 inch	2-1/4 inch	2-1/4 inch	4-9/16 inch	1-7/16 inch	1-7/16 inch	1-7/16 inch

