



Ecoclick Starters

S16 70-125W 240V UNP/20X10CT


Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

Product data

Operating and Electrical	
Power Consumption	125 70 W
Voltage (nom.)	240 V
Mechanical and Housing	
Housing Colour	White
Net Weight (Piece)	7.000 g
Product Data	
Order product name	S16 70-125W 240V UNP/20X10CT
Full product name	S16 70-125W 240V UNP/20X10CT

Full EOC	871150090356331
Order code	90356331
Material no. (12 NC)	928390930371
Local order code	S1610WBNEW
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500903563
Numerator – packs per outer box	200
EAN/UPC - Case	8711500903587

Dimensional drawing



Product	C (max)	E (max)
S16 70-125W 240V UNP/20X10CT	40.3 mm	21.5 mm