

# Ecoclick Starters

## S10 4-65W SIN 220-240V WH EUR/1000


Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

### Product data

Operating and Electrical	
Power Consumption	4.65 W
Voltage (nom.)	220-240 V
Mechanical and Housing	
Housing Colour	White
Net Weight (Piece)	7.000 g
Product Data	
Order product name	S10 4-65W SIN 220-240V WH EUR/1000
Full product name	S10 4-65W SIN 220-240V WH EUR/1000

Full EOC	871150069769128
Order code	928392220229
Material no. (12 NC)	928392220229
Local order code	S101000W
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500697691
Numerator – packs per outer box	1,000
EAN/UPC - Case	8711500697707

### Dimensional drawing



Product	C (max)	E (max)
S10 4-65W SIN 220-240V WH EUR/1000	40.3 mm	21.5 mm