



# Ecoclick Starters

## S10 4-65W SIN 220-240V WH EUR/20X10CT

Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.


### Product data

Operating and Electrical	
Power Consumption	4 65 W
Voltage (nom.)	220-240 V
Mechanical and Housing	
Housing Colour	White
Net Weight (Piece)	7.000 g
Approval and Application	
CE mark	Yes
Product Data	
Order product name	S10 4-65W SIN 220-240V WH EUR/20X10CT

Full product name	S10 4-65W SIN 220-240V WH EUR/20X10CT
Full EOC	871150069769131
Order code	928392220238
Material no. (12 NC)	928392220238
Local order code	S1010W
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8711500697691
Numerator – packs per outer box	200
EAN/UPC - Case	8711500697905

## Ecoclick Starters

### Dimensional drawing



Product	C (max)	E (max)
S10 4-65W SIN 220-240V WH EUR/20X10CT	40.3 mm	21.5 mm

