



Ceramalux ALTO

C1000S52/ALTO

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050


Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Chromaticity Coordinate X (Nom)	515
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	121.5 lm/W
Luminous Efficacy (rated) (Nom)	135 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Power Consumption	1,003 W
Lamp Current (Nom)	4.7 A
Voltage (Nom)	250 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	E25
Net Weight (Piece)	0.002 lb
Approval and Application	
Mercury (Hg) Content (Nom)	32 mg
Product Data	
Order product name	C1000S52/ALTO
Full product name	C1000S52/ALTO
Order code	368837
Material Nr. (12NC)	928601139205
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677368838
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677368833

Ceramalux ALTO

Dimensional drawing



Product
C1000S52/ALTO

