



Ceramalux ALTO

C200S66/ALTO 12PK

These lamps pass the EPA's TCLP test for non-hazardous materials. Ideal for industrial applications, warehouses, post top applications and parking lots.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® (ALTO)
Light Technical	
Chromaticity Coordinate X (Nom)	521
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	104 lm/W
Luminous Efficacy (rated) (Nom)	115 lm/W
Color rendering index (CRI)	16
Operating and Electrical	
Power Consumption	200.8 W
Lamp Current (Nom)	2.4 A
Voltage (Nom)	100 V
Mechanical and Housing	
Bulb Finish	Clear


Bulb Material	Hard Glass
Bulb Shape	ED18
Net Weight (Piece)	0.366 lb

Approval and Application	
Mercury (Hg) Content (Max)	31 mg

Product Data	
Order product name	C200S66/ALTO 12PK
Full product name	C200S66/ALTO 12PK
Order code	467225
Material Nr. (12NC)	928601139590
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467227
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467222

Ceramalux ALTO

Dimensional drawing



Product
C200S66/ALTO 12PK

