



# Ceramalux Non-ALTO

## C100S54/M 3PK

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

### Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

| General Information                |                                   |
|------------------------------------|-----------------------------------|
| Cap-Base                           | E26 [Single Contact Medium Screw] |
| Operating Position                 | UNIVERSAL [Any or Universal (U)]  |
| Light Technical                    |                                   |
| Chromaticity Coordinate X (Nom)    | 520                               |
| Chromaticity Coordinate Y (Nom)    | 420                               |
| Correlated Color Temperature (Nom) | 2100 K                            |
| Luminous Efficacy (Rated) (Min)    | 84 lm/W                           |
| Luminous Efficacy (rated) (Nom)    | 92 lm/W                           |
| Color rendering index (CRI)        | 18                                |
| Operating and Electrical           |                                   |
| Power Consumption                  | 100.4 W                           |
| Lamp Current (Nom)                 | 2.1 A                             |
| Voltage (Nom)                      | 55 V                              |
| Mechanical and Housing             |                                   |
| Bulb Finish                        | Clear                             |

| Bulb Material                   | Hard Glass                  |
|---------------------------------|-----------------------------|
| Bulb Shape                      | BD17                        |
| Net Weight (Piece)              | 0.249 lb                    |
| Approval and Application        |                             |
| Mercury (Hg) Content (Max)      | 22 mg                       |
| Product Data                    |                             |
| Order product name              | 100W BD17 HP SODIUM HID CLR |
| Full product name               | C100S54/M 3PK               |
| Order code                      | 460824                      |
| Material Nr. (12NC)             | 928601143514                |
| Numerator - Quantity Per Pack   | 1                           |
| EAN/UPC - Product/Case          | 046677460822                |
| Numerator - Packs per outer box | 3                           |
| EAN/UPC - Case                  | 50046677460827              |

Ceramalux Non-ALTO

Dimensional drawing

| Product                     | D           | C (max)     |
|-----------------------------|-------------|-------------|
| 100W BD17 HP SODIUM HID CLR | 2-3/16 inch | 5-7/16 inch |

