



Ceramalux Non-ALTO

C100S54/M PH 12PK

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	520
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	84 lm/W
Luminous Efficacy (rated) (Nom)	92 lm/W
Color rendering index (CRI)	18
Operating and Electrical	
Power Consumption	100.4 W
Lamp Current (Nom)	2.1 A
Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	BD17
Net Weight (Piece)	73.000 g
Approval and Application	
Mercury (Hg) Content (Max)	22 mg
Product Data	
Order product name	C100S54/M PH 12PK
Full product name	C100S54/M PH 12PK
Order code	467274
Material Nr. (12NC)	928601143590
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467272
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467277

Ceramalux Non-ALTO

Dimensional drawing

Product	D	C (max)
C100S54/M PH 12PK	55 mm	138 mm

