



Ceramalux Non-ALTO

C100S54/M PH 12PK

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	520
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	84 lm/W
Luminous Efficacy (rated) (Nom)	92 lm/W
Color rendering index (CRI)	18
Operating and Electrical	
Power Consumption	100.4 W
Lamp Current (Nom)	2.1 A
Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	BD17
Net Weight (Piece)	0.161 lb

Approval and Application	
Mercury (Hg) Content (Max)	22 mg

Product Data	
Order product name	C100S54/M PH 12PK
Full product name	C100S54/M PH 12PK
Order code	467274
Material Nr. (12NC)	928601143590
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467272
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467277

Ceramalux Non-ALTO

Dimensional drawing

Product	D	C (max)
C100S54/M PH 12PK	2-3/16 inch	5-7/16 inch

