



Ceramalux Instant Restrike

C250S50/2 1/12PK

Dual arc-tube delivers 40,000 hour rated average life as compared to 24,000 hour rated average life for standards HPS lamps. Ideal for industrial applications, warehouses, post top applications and parking lots.

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	521
Chromaticity Coordinate Y (Nom)	415
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	102.6 lm/W
Luminous Efficacy (rated) (Nom)	114 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Power Consumption	251 W
Lamp Current (Nom)	3 A
Voltage (Nom)	100 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	ED18
Net Weight (Piece)	0.001 kg

Approval and Application	
Mercury (Hg) Content (Nom)	47 mg

Product Data	
Order product name	C250S50/2 1/12PK
Full product name	C250S50/2 1/12PK
Order code	377176
Material Nr. (12NC)	928601145501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677377175
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677377170

Ceramalux Instant Restrike

Dimensional drawing

Product	D	C (max)
C250S50/2 1/12PK	2.25 inch	9.75 inch

