



Ceramalux Instant Restrike

C100S54/2 1/12PK

Dual arc-tube delivers 40,000 hour rated average life as compared to 24,000 hour rated average life for standards HPS lamps. Ideal for industrial applications, warehouses, post top applications and parking lots.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	520
Chromaticity Coordinate Y (Nom)	420
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	84 lm/W
Luminous Efficacy (rated) (Nom)	93 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Power Consumption	100.4 W
Lamp Current (Nom)	2.1 A
Voltage (Nom)	55 V

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED-23 1/2
Net Weight (Piece)	0.002 lb
Approval and Application	
Mercury (Hg) Content (Max)	44.4 mg
Product Data	
Order product name	C100S54/2 1/12PK
Full product name	C100S54/2 1/12PK
Order code	265603
Material Nr. (12NC)	928601145701
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677265601
Numerator - Packs per outer box	12

Ceramalux Instant Restrike

EAN/UPC - Case	50046677265606
----------------	----------------

Dimensional drawing

Product	D	C (max)
C100S54/2 1/12PK	2.938 inch	7.75 inch

