



Ceramalux Non-ALTO

C150S55/M 12PK

Philips Ceramalux lamps provide efficient lighting solutions for industrial applications, warehouses, post top applications and parking lots.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Light Technical	
Chromaticity Coordinate X (Nom)	514
Chromaticity Coordinate Y (Nom)	424
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	96 lm/W
Luminous Efficacy (rated) (Nom)	106 lm/W
Color rendering index (CRI)	17
Operating and Electrical	
Power Consumption	150.6 W
Lamp Current (Nom)	3.2 A
Voltage (Nom)	55 V
Mechanical and Housing	
Bulb Finish	Clear

Bulb Material	Hard Glass
Bulb Shape	BD17
Net Weight (Piece)	0.165 lb

Approval and Application

Mercury (Hg) Content (Max)	17 mg
----------------------------	-------

Product Data

Order product name	SON 150W E26 BD54 CL SL/12
Full product name	C150S55/M 12PK
Order code	467316
Material Nr. (12NC)	928601147490
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677467319
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467314

Ceramalux Non-ALTO

Dimensional drawing

Product	D	C (max)
SON 150W E26 BD54 CL SL/12	2-3/16 inch	5-3/4 inch

