



# Switch Start Metal Halide Standard

## MH175/U UPC 3PK

High performance, Long life and Superior light quality. A compact, energy efficient metal halide lamp that provides crisp, sparkling light with long life and high efficiency.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: [www.lamprecycle.org](http://www.lamprecycle.org) or 1-800-555-0050

### Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	10,000 hour(s)
Light Technical	
Color Code	640 [CCT of 4000K]
Color Designation	Cool White (CW)
Luminous Efficacy (rated) (Nom)	84 lm/W
Chromaticity Coordinate X (Nom)	0.375
Chromaticity Coordinate Y (Nom)	0.400
Correlated Color Temperature (Nom)	4000 K

Luminous Efficacy (Rated) (Min)	70 lm/W
Color rendering index (CRI)	65
Operating and Electrical	
Lamp Current (Nom)	1.5 A
Voltage (Nom)	132 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED28

## Switch Start Metal Halide Standard

### Approval and Application


Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	28 mg

### Product Data

Order product name	175W ED28 Mogul Base Metal Halide
Full product name	MH175/U UPC 3PK
Order code	140855

Material Nr. (12NC)	928601150312
Net Weight (Piece)	0.002 lb
EAN/UPC - Product/Case	046677253592
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677140859

### Dimensional drawing



Product	D	C (max)
175W ED28 Mogul Base Metal Halide	3.5 inch	8.313 inch

