



Switch Start Metal Halide Standard

MH175/C/U 12PK

High performance, Long life and Superior light quality. A compact, energy efficient metal halide lamp that provides crisp, sparkling light with long life and high efficiency.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA: 21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Light Technical	
Luminous Flux	8,645 lm
Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.39
Correlated Color Temperature (Nom)	3900 K
Luminous Efficacy (Rated) (Min)	64 lm/W
Luminous Efficacy (rated) (Nom)	76 lm/W
Color rendering index (CRI)	>60

Operating and Electrical	
Power Consumption	175 W
Wattage Equivalent	175 W
Warm-up time to 60% light	<120 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Coated glass
Bulb Material	Hard Glass
Bulb Shape	BD17

Switch Start Metal Halide Standard

Net Weight (Piece)	0.002 lb
Approval and Application	
Mercury (Hg) Content (Max)	30 mg
Product Data	
Order product name	MH175/C/U 12PK
Full product name	MH175/C/U 12PK

Order code	287284
Material Nr. (12NC)	928601150403
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677287283
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677287288

Dimensional drawing

Product	D (max)	C (max)
MH175/C/U 12PK	3-9/16 inch	8-1/8 inch

