



Ceramalux ALTO Non-Cycling

C250S50/ALTO NC HPS 1/12PK

Philips Ceramalux High Pressure Sodium Non-Cycling Lamps are a better value than standard high pressure sodium lamps, with longer life and reduced maintenance cost.

Warnings and Safety

- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data


General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ALTO® Non-Cycling
Light Technical	
Chromaticity Coordinate X (Nom)	0.523
Chromaticity Coordinate Y (Nom)	0.415
Correlated Color Temperature (Nom)	2100 K
Luminous Efficacy (Rated) (Min)	102 lm/W
Luminous Efficacy (rated) (Nom)	114 lm/W
Color rendering index (CRI)	21
Operating and Electrical	
Power Consumption	251 W
Lamp Current (Nom)	1.8 A

Voltage (Nom)	100 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED18
Net Weight (Piece)	0.353 lb
Approval and Application	
Mercury (Hg) Content (Nom)	3.36 mg
Product Data	
Order product name	C250S50/ALTO NC HPS 1/12PK
Full product name	C250S50/ALTO NC HPS 1/12PK
Order code	467340
Material Nr. (12NC)	928601156190
Numerator - Quantity Per Pack	1

Ceramalux ALTO Non-Cycling

EAN/UPC - Product/Case	046677467340
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677467345

Dimensional drawing



Product	D	L	C (max)
C250S50/ALTO NC HPS 1/12PK	2.25 inch	5.750 inch	9.75 inch

