



Pulse Start Metal Halide Standard

MS250/U/PS 12/1

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Light Technical	
Luminous Flux	13,650 lm
Color Designation	4000 Kelvin
Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.395
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (Rated) (Min)	70 lm/W
Luminous Efficacy (rated) (Nom)	84 lm/W
Color rendering index (CRI)	>65


Operating and Electrical	
Power Consumption	250 W
Wattage Equivalent	250 W
Warm-up time to 60% light	<120 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED28

Pulse Start Metal Halide Standard

Net Weight (Piece)	0.002 lb
Approval and Application	
Mercury (Hg) Content (Max)	32 mg
Product Data	
Order product name	MS250/U/PS 12PK
Full product name	MS250/U/PS 12/1

Order code	232801
Material Nr. (12NC)	928601165802
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677232801
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677232806

Dimensional drawing



Product	D (max)	C (max)
MS250/U/PS 12PK	3-5/8 inch	8-1/8 inch

