



Switch Start Metal Halide Standard

MH400/U 1/6PK

High performance, Long life and Superior light quality. A compact, energy efficient metal halide lamp that provides crisp, sparkling light with long life and high efficiency.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Life to 50% Failures (Nom)	20,000 hour(s)
Light Technical	
Color Code	640 [CCT of 4000K]
Color Designation	Cool White (CW)
Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.395
Correlated Color Temperature (Nom)	3900 K
Luminous Efficacy (Rated) (Min)	85 lm/W


Luminous Efficacy (rated) (Nom)	98 lm/W
Color rendering index (CRI)	65
Operating and Electrical	
Power Consumption	400 W
Lamp Current (Nom)	3.25 A
Voltage (Nom)	135 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED37

Switch Start Metal Halide Standard

Net Weight (Piece)	0.002 lb
Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	38 mg
Product Data	
Order product name	MH400/U 1/6PK
Full product name	MH400/U 1/6PK

Full product code	871829111668400
Order code	274498
Material Nr. (12NC)	928601172301
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677274498
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677274493

Dimensional drawing



Product	D	C (max)
MH400/U 1/6PK	4.625 inch	11.5 inch

