



MasterColor CDM ED17 Protected

MHC100/U/MP/3K ELITE

Direct retrofit with immediate energy savings!. Range of protected, high-efficiency long life ceramic metal halide lamps with a stable color over lifetime and a crisp, sparkling light to be used in open fixtures.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Operating Position	UNIVERSAL [Any or Universal (U)]
Features	ELITE
Life to 50% Failures (Nom)	16,000 hour(s)

Light Technical	
Color Code	930 [CCT of 3000K]
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	0.434
Chromaticity Coordinate Y (Nom)	0.401
Correlated Color Temperature (Nom)	3000 K

Luminous Efficacy (Rated) (Min)	94 lm/W
Luminous Efficacy (rated) (Nom)	100 lm/W
Color rendering index (CRI)	90

Operating and Electrical	
Lamp Current (Nom)	1.1 A
Voltage (Nom)	101 V


Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	ED17P [ED-17P Protected]

MasterColor CDM ED17 Protected

Net Weight (Piece)	0.002 lb
Approval and Application	
Mercury (Hg) Content (Max)	10.1 mg
Product Data	
Order product name	MHC100/U/MP/3K ELITE
Full product name	MHC100/U/MP/3K ELITE


Order code	423673
Material Nr. (12NC)	928601174001
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677423674
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677423679

Dimensional drawing



Product	C (max)	
MHC100/U/MP/3K ELITE	2.125 inch	5.438 inch

Lifetime



LDLE_D-MHC-P_0005-Life expectancy diagram

