



Switch Start Metal Halide Protected

MP1000/BU 6PK

An efficient, protected "O" rated lighting solution that is suitable for open-rated fixtures. Ideal for both indoor and outdoor applications.

Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)
- Lamp contains mercury.
- Manage in Accord with Disposal Laws.
- See: www.lamprecycle.org or 1-800-555-0050

Product data

General Information	
Cap-Base	EX39 [Exclusionary Mogul Screw]
Operating Position	H15 [Hanging +/-15D or Base Up (BU)]
Life to 50% Failures (Nom)	12,000 hour(s)
Light Technical	
Color Code	635 [CCT of 3500K]
Color Designation	White (WH)
Chromaticity Coordinate X (Nom)	405
Chromaticity Coordinate Y (Nom)	390
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	107 lm/W


Color rendering index (CRI)	65
Operating and Electrical	
Lamp Current (Nom)	4.1 A
Voltage (Nom)	263 V
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	BT56
Net Weight (Piece)	0.002 lb

Switch Start Metal Halide Protected

Approval and Application	
Mercury (Hg) Content (Nom)	150 mg
Product Data	
Order product name	MP1000/BU 6PK
Full product name	MP1000/BU 6PK
Order code	281188

Material Nr. (12NC)	928601179601
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677281182
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677281187

Dimensional drawing



Product	D	C (max)
MP1000/BU 6PK	7 inch	15.375 inch

